




REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
B4	29MAY2012	REVISED PER ECO-12-009257	DD	DS
B5	16JAN2014	REVISED PER ECO-13-020287	DD	DS




776267-1 & 1-776267-1
KEY LOCATION
SCALE 2:1



776267-2 & 1-776267-2
KEY LOCATION
SCALE 2:1




776267-4 & 1-776267-4
KEY LOCATION
SCALE 2:1





776267-5 & 1-776267-5
KEY LOCATION
SCALE 2:1


- △ ACCEPTS #4 SELF TAPPING THREAD FORMING SCREWS OR METRIC EQUIVALENT. DRIVE TO 0.4 N-m MINIMUM.
- △ HOUSING COLORS ARE MECHANICALLY KEYS TO MATE ONLY WITH IDENTICALLY COLORED PLUG ASSEMBLIES.
- 3. HEADER MATES TO PLUG ASSEMBLY 776273 WHICH USES REELED TERMINAL 770520 OR LOOSE PIECE TERMINAL 770854
- △ MATERIAL: GASKET - SILICONE
HEADER HOUSING - GLASS FILLED PBT
PINS - TIN OR GOLD PLATED BRASS
- △ DATE CODE TO BE BRANDED ON THIS SURFACE PER TE SPEC 102-60. USE 5 DIGIT CODE: FIRST 2 DIGITS = YEAR, SECOND 2 DIGITS = WEEK, LAST DIGIT = DAY.




776267-1 SHOWN




SECTION A-A
OPTIONAL CONSTRUCTION IF
THICKNESS IS GREATER THEN 2.0



SECTION A-A
OPTIONAL CONSTRUCTION IF
THICKNESS IS GREATER THEN 2.0



RECOMMENDED MOUNTING HOLE LAYOUT
FOR 5.0 MAXIMUM THICK PANEL



RECOMMENDED PC BOARD LAYOUT
FOR 1.57 PC BOARD

HEADER HOUSING COLOR	DESCRIPTION	PART NUMBER
BLUE	DURAGOLD PLATED	1-776267-5
GRAY	DURAGOLD PLATED	1-776267-4
NATURAL	DURAGOLD PLATED	1-776267-2
BLACK	DURAGOLD PLATED	1-776267-1
BLUE	TIN PLATED	776267-5
GRAY	TIN PLATED	776267-4
NATURAL	TIN PLATED	776267-2
BLACK	TIN PLATED	776267-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:	OWN: D. DRUMMOND 18AUG2010	CHK: D. STRAUSSER 18AUG2010	APVD: D. STRAUSSER 18AUG2010
mm	0 PLC ±0.2 2 PLC ±0.13 3 PLC ±0.1 4 PLC ±0.1	PRODUCT SPEC: 108-1329	APPLICATION SPEC: 114-16016	WEIGHT: -
MATERIAL: 4	FINISH: 4	SIZE: 114-16016	SCALE: 4:1	SHEET 1 OF 1

TE Connectivity
HEADER ASSEMBLY, 14 POSITION, RIGHT ANGLE, AMPSEAL
A100779C=776267
CUSTOMER DRAWING