

Accessories
VG 21 HQ MS68 9-13**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Currently, heavy-duty connectors are used wherever there is a need for a secure, simple and time-saving assembly of machinery and facilities.

The connector housings are made of die-cast aluminium and offer excellent protection against dirt, moisture and mechanical stress.

Special modular connectors make it possible to integrate signals, power supply, pneumatics, and data connections into a single connector.

With the RockStar® heavy-duty connectors, Weidmüller offers a product line with many patented innovations that is oriented towards the future.

The RockStar® product line defines new standards with the comprehensive depth and width of its features. What other suppliers offer only as a custom configuration, Weidmüller supplies in its standard product line.

As a result, selecting the proper connector is now easier than ever. You save both time and money. And your work flow is optimised. Thus you can strengthen your position on the market and leverage your competitive advantage

General ordering data

Type	VG 21 HQ MS68 9-13
Order No.	1016090000
Version	Heavy Duty Connectors, Accessories, cable glands, Brass, nickel-plated
GTIN (EAN)	4032248725540
Qty.	1 pc(s).

Datenblatt

**Accessories
VG 21 HQ MS68 9-13**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 40 g

Temperatures

Operating temperature -40 °C...+100 °C

General data

AF size	30 mm	Cable diameter, max.	13 mm
Cable diameter, min.	9 mm	Cable gland	PG 21
Internal thread	PG 21	Material	Brass, nickel-plated
Protection degree	IP 68	Sealing material	TPE
Size	HQ	Tightening torque, max.	15 Nm

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Approvals

Approvals



ROHS Conform