

**Device markers
THM GEW 17/9 WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Type	THM GEW 17/9 WS
Order No.	105980000
Version	Device markers, Label, 17 x 9 mm, Vinyl-coated cotton fabric, Colour: White
GTIN (EAN)	4032248808199
Qty.	1 pc(s).

Device markers THM GEW 17/9 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	17 mm	Width	9 mm
Net weight	676 g		

General data

Adhesive	Natural rubber adhesive	Colour	White
Material	Vinyl-coated cotton fabric	Material colour according to resistance code	9
Number per roll	10,000	Number per sheet	10,000
Operating temperature range, max.	80 °C	Operating temperature range, min.	-29 °C
Printing method	Thermotransfer	UL 94 flammability rating	HB
UL 969 flammability rating	No		

Classifications

ETIM 3.0	EC001288	UNSPSC	55-12-16-00
eClass 5.1	27-14-91-29	eClass 6.2	27-14-91-29
eClass 7.1	27-14-91-29		

Approvals

Approvals	
ROHS	Conform

Downloads

M-Print® PRO configuration file [lab_thm_gew_17_9_mcf.zip](#)