

PCB terminal block - SPT 5/ 2-V-7,5-ZB BU - 1764927

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

PCB terminal block, Nominal current: 41 A, Nom. voltage: 1000 V, Pitch: 7.5 mm, Number of positions: 2, Connection method: Spring-cage conn., Mounting: Soldering, Conductor/PCB connection direction: 90 °

Key commercial data

package_quantity	50
GTIN	4046356418614

Technical data

Dimensions

Pitch	7.5 mm
Dimension a	7.5 mm
Pin dimensions	1,7 x 0,8
Pin spacing	7.5 mm
Hole diameter	2.1 mm

General

Range of articles	SPT 5/..-V
Rated surge voltage (III/3)	8 kV
Rated surge voltage (III/2)	8 kV
Rated surge voltage (II/2)	6 kV
Rated voltage (III/3)	800 V
Rated voltage (III/2)	1000 V
Rated voltage (II/2)	1000 V
Connection in acc. with standard	EN-VDE
Nominal current I_N	41 A
Nominal cross section	6 mm ²
Solder pin surface	Sn
Stripping length	15 mm
Number of positions	2

Connection data

Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	8
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.25 mm ²

PCB terminal block - SPT 5/ 2-V-7,5-ZB BU - 1764927

Technical data

Connection data

2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm ²
Minimum AWG according to UL/CUL	24
Maximum AWG according to UL/CUL	8

classifications

eCl@ss

eCl@ss 4.0	27141109
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643


UNSPSC

UNSPSC 6.01	30211801
UNSPSC 7.0901	39121432
UNSPSC 11	39121432
UNSPSC 12.01	39121432
UNSPSC 13.2	39121432

approvals

UL Recognized / SEV / cUL Recognized / CCA / IECCEB Scheme / GOST / UL Recognized / cUL Recognized / GOST / cULus Recognized /


Approval details

UL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	36 A	36 A
mm ² /AWG/kcmil	24-8	24-8


PCB terminal block - SPT 5/ 2-V-7,5-ZB BU - 1764927


approvals


SEV	
Nominal voltage UN	1000 V
Nominal current IN	41 A
mm ² /AWG/kcmil	6

cUL Recognized 		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	36 A	36 A
mm ² /AWG/kcmil	24-8	24-8

CCA	
Nominal voltage UN	1000 V
Nominal current IN	41 A
mm ² /AWG/kcmil	6


IECEE CB Scheme 	
Nominal voltage UN	1000 V
Nominal current IN	41 A
mm ² /AWG/kcmil	6


GOST 	
--	--

		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	36 A	36 A
mm ² /AWG/kcmil	24-8	24-8

PCB terminal block - SPT 5/ 2-V-7,5-ZB BU - 1764927

approvals

		
Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	36 A	36 A
mm ² /AWG/kcmil	24-8	24-8



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>