

Conrad BN		The proportion of Ingredients (viscosity)
232630	200CPS	TSF451-100 w/ 75% + TSF451-1000 w/ 25%
232631	250CPS	TSF451-100 w/ 70% + TSF451-1000 w/ 30%
232632	300CPS	TSF451-100 w/ 65% + TSF451-1000 w/ 35%
232633	350CPS	TSF451-100 w/ 60% + TSF451-1000 w/ 40%
232634	400CPS	TSF451-100 w/ 55% + TSF451-1000 w/ 45%
232635	450CPS	TSF451-100 w/ 50% + TSF451-1000 w/ 50%
232636	500CPS	TSF451-100 w/ 45% + TSF451-1000 w/ 55%
232638	600CPS	TSF451-100 w/ 35% + TSF451-1000 w/ 65%
232639	700CPS	TSF451-100 w/ 25% + TSF451-1000 w/ 75%
232640	800CPS	TSF451-100 w/ 15% + TSF451-1000 w/ 85%
232641	1000CPS	TSF451-1000 w/ 100%
232642	3000CPS	TSF451-1000 w/ 70% + VISC-30M w/ 30%
232643	5000CPS	TSF451-1000 w/ 60% + VISC-30M w/ 40%
232644	7000CPS	TSF451-1000 w/ 55% + VISC-30M w/ 45%
232646	10000CPS	VISC-10M w/ 100%
232647	20000CPS	VISC-10M w/ 50% + VISC-30M w/ 50%
232571	30000CPS	VISC-30M w/ 100%
232649	50000CPS	VISC-10M w/ 75% + VISC-60M w/ 25%