


Nominal Voltage :	6,0 V	
Nominal Capacity	800 mAh	at 0.2C discharge to 1.0V after 16h/0.1C charge*
Weight ± 5 g :	65 g	
Int. Resistance :	≤190 mΩ	at 1 kHz

Charge Characteristics

Standard Charge :	16 h x 0.1 C (80mA)
Fast Charge :	2.5 h x 0.5 C (400mA)

Discharge Characteristics


end 1.0 V	
0.2 C (160mA)*	800 mAh
1.0 C (800mA)*	720 mAh



Storage Temperature :	min -20 °C	max 40°C
Operating Temperature :	min -10 °C	max 45°C
Cycle life test :	IEC 61436	> 500 cycles

Dimensions

Height (H) max.	44.50 mm
Diameter (D) max.	11.00 mm
Width (W) max.	53.50 mm



Don't disassemble and don't mix with used or other battery types.
 Don't dispose to fire.
 Remove batteries when not in use for long periods.

* test condition: 20 ± 5°C