

**Cable glands
VG PG36-MS54 ZR 24-33**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Each size of this standard cable gland consists of multiple, separable seal inserts (onion-ring shaped). By separating these individual inserts, it becomes possible to install cables of varying diameters (from 4 mm to 41 mm) into the cable gland.

General ordering data

Type	VG PG36-MS54 ZR 24-33
Order No.	1009650000
Version	cable glands, Brass, nickel-plated, External thread: PG 36
GTIN (EAN)	4032248714421
Qty.	10 pc(s).

Datenblatt

**Cable glands
VG PG36-MS54 ZR 24-33**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	39 mm	Net weight	264 g
--------	-------	------------	-------

General information

AF size 1	47 mm	AF size 2	50 mm
Cable gland	PG	Clamping range, max.	33 mm
Clamping range, min.	24 mm	External thread	PG 36
Length of thread	9 mm	Material	Brass, nickel-plated
Notch multi-layer sealing diameter 1	24 mm	Notch multi-layer sealing diameter 2	27 mm
Notch multi-layer sealing diameter 3	30 mm	Notch multi-layer sealing diameter 4	33 mm
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Seal insert	NBR	Torque for cap nut, max.	6.7 Nm
Torque for cap nut, min.	6.7 Nm	Torque for connecting adapter, max.	10 Nm
Torque for connecting adapter, min.	10 Nm		

Classifications

eClass 6.2	27-18-92-34	eClass 7.1	27-18-92-34
------------	-------------	------------	-------------

Product information

Descriptive text ordering data	D1-D4 are the removable seal incisions from 4 mm to 41 mm.
--------------------------------	--

Approvals

Approvals



ROHS	Conform
------	---------