

Terminal markers MF-W 9/4.2F MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



MultiFit is the Weidmüller marker system used for other makes of terminals in 4, 5, 6, 6.5, 7.5, 8, 10 and 12 mm pitches. Similar to the Weidmüller dekafix, the markers of the MultiFit family are available ready-for-use with standard printing.

We recommend to carry out a test with sample markers on the terminals used when using MultiFit for the first time.

- One marker, suitable for different makes of terminals.
- Ready-to-use markers with standard printing
- Blank markers for printing with the SMark laser, PrintJet ADVANCED, plotter or MC-Mobilo,
- Delivery of individually printed markers according to customer CAE data or specifications
- One marking system for all applications

General ordering data

Type	MF-W 9/4.2F MC NE WS
Order No.	1011430000
Version	Terminal markers, MultiCard, 9 x 4.2 mm, Polyamide 66, Colour: White
GTIN (EAN)	4032248717804
Qty.	500 pc(s).

Datenblatt

Terminal markers MF-W 9/4.2F MC NE WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	9 mm	Width	4.2 mm
Net weight	0.172 g		

General data

Application/manufacturer	WAGO, Legrand	Colour	White
Material	Polyamide 66	Material colour according to resistance code	9
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-2		

Classifications

ETIM 3.0	EC000761	UNSPSC	30-21-18-01
eClass 6.2	27-14-11-37	eClass 7.1	27-14-11-37

Approvals

Approvals	
ROHS	Conform

Downloads

MPP Config	mc_mf-w_9_4-2_f_mcf.zip
------------	---

Datenblatt

**Terminal markers
MF-W 9/4.2F MC NE WS**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

Example of use



Drawing

