

**Bolt-type screw terminals, Accessories  
WQL 2 WFF35**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



The comprehensive range of bolt-type screw terminals offers secure connections for all power transmission applications.

Connections from 10 mm<sup>2</sup> to 300 mm<sup>2</sup> are possible. The conductors are attached to the terminals using crimped cable lugs and each connection secured by tightening the hexagonal nut.

Bolt-type screw terminals with threads from M5 to M16 can be used depending on the conductor cross-section. A low voltage drop and the use of a self-extinguishing material with a V-0 (UL 94) flammability rating guarantee maximum safety.

All bolt-type screw terminals have been tested according to international railway standards (EN 50343, EN 50155, NF F61-017, NF16-101; Ria 20) and comply with the requirements of those standards.

**General ordering data**

Type	WQL 2 WFF35
Order No.	<a href="#">1064900000</a>
Version	Bolt-type screw terminals, Accessories, Cross-connector, No. of poles: 2
GTIN (EAN)	4008190112745
Qty.	5 pc(s).

## Bolt-type screw terminals, Accessories WQL 2 WFF35

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

Length	42 mm	Width	15 mm
Height	3 mm	Net weight	14.22 g

### Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

### Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
--------------------------	----	---------------------	-----------------

### Rated data

Rated current	125 A
---------------	-------

### Material data

Material	Copper - zinc	Colour	Grey
----------	---------------	--------	------

### System specifications

Product family	Bolt-type screw terminals, Accessories
----------------	---

### Classifications

ETIM 3.0	EC000489	UNSPSC	30-21-18-01
eClass 5.1	27-14-11-40	eClass 6.2	27-14-11-40
eClass 7.1	27-14-11-40		

### Approvals

Approvals	
ROHS	Conform