


M1: Transmission /M Log Mag 10.0 dB/ Ref -20.00 dB
 M2: Reflection Log Mag 10.0 dB/ Ref -50.00 dB




Start 300.000 MHz

Stop 1 000.000 MHz

Marker	Freq [MHz]	Ch 1 [dB]	Ch 2 [dB]
1	450.000	-4.12	-5.64
2	462.000	-5.73	-4.91
3	370.120	-5.01	-3.63
4	430.000	-5.00	-2.79
5	100.000		-1.02
6	200.000		-1.02
7	300.000		-1.02
8	300.000		-1.02

M1: Transmission /M Log Mag 10.0 dB/ Ref -20.00 dB
M2: Reflection Log Mag 10.0 dB/ Ref -50.00 dB




Start 50.000 MHz

Stop 300.000 MHz

Marker	Freq (MHz)	Ch 1 (dB)	Ch 2 (dB)
1	100.000	-21.25	-0.31
2	174.000	-0.95	-9.29
3	230.000	-0.07	-10.35
4	300.000	-5.23	-2.50
5	100.000		-0.31
6	200.000		-7.32
7	300.000		-2.50
8	300.000		-2.50

M1: Transmission /M Log Mag 10.0 dB/ Ref -20.00 dB
 M2: Reflection, Log Mag 10.0 dB/ Ref -50.00 dB



Start 50.000 MHz

Stop 300.000 MHz

Marker	Freq (MHz)	Ch 1 (dB)	Ch 2 (dB)
1	100.000	-1.97	-5.00
2	174.000	-13.37	-0.73
3	230.000	-30.00	-0.52
4	300.000	-26.12	-0.50