

Specification (技术参数):

Element (单体): Back Electret Condenser (背极式驻极体)

Polar Pattern (指向性): Uni-directional (单指向)

Frequency Response (频率响应): 50Hz~18kHz

Sensitivity (灵敏度): $-45\text{dB} \pm 3\text{dB}$ ($0\text{dB} = 1\text{V}/\text{Pa}$ at 1kHz)


Output Impedance (输出阻抗): $250\Omega \pm 30\%$

Max. Input SPL (最大声压级): 136 dB (1kHz at 1% T.H.D)


S/N Ratio (信噪比): 60dB

Phantom Power Requirement (使用电压): 9V~52V DC and 1.5V Battery

Battery Type (电池规格): AA/UM3, 1.5V



Frequency Response Graph (频率响应曲线)



Uni-directional
单指向
(at 1kHz)