


Crimping contact HDC-C-HE-BM0.5AG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Crimps provide a electrical and mechanical connection between wire and contact that is both secure and reliable. The optimal crimp connection is gas-tight and corrosion-resistant.

General ordering data

Type	HDC-C-HE-BM0.5AG
Order No.	1201100000
Version	Heavy Duty Connectors, Contact, HE, HEE, HQ, MixMate, CM HE, CM BUS (CSB), Female, Conductor cross-section, max.: 0.5, turned, Copper alloy
GTIN (EAN)	4008190142698
Qty.	100 pc(s).

Datenblatt

**Crimping contact
HDC-C-HE-BM0.5AG**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight	1.61 g	Diameter	4.5 mm
------------	--------	----------	--------

General data

Contact diameter, male Ø	2.5 mm	Production methods	turned
Stripping length, rated connection	7.5 mm	Type	Female
Type of connection	Crimp connection	Material	Copper alloy
Series	HE	Surface finish	silver
Volume resistance	≤ 2mΩ		

Classifications

ETIM 3.0	EC000796	UNSPSC	30-21-18-01
eClass 5.1	27-14-34-19	eClass 6.2	27-26-12-02
eClass 7.1	27-44-02-04		

Product information

Descriptive text technical data	Surface layer thickness: 2-3 µm
Descriptive text accessories	For further accessories, see chapter J - tools, see chapter K

Approvals

Approvals



ROHS Conform

Datenblatt

**Crimping contact
HDC-C-HE-BM0.5AG**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Zeichnungen

