

## Cable markers CLI M 2-4 BR/WS 1 MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

### Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm<sup>2</sup>
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

### General ordering data

|            |   |
|------------|---|
| Type       | CLI M 2-4 BR/WS 1 MP  |
| Order No.  | <a href="#">1733651506</a>  |
| Version    | Cable markers, 4 x 11.3 mm, PVC, soft, without Cadmium, Colour: Brown |
| GTIN (EAN) | 4032248451111   |
| Qty.       | 100 pc(s).  |

## Cable markers CLI M 2-4 BR/WS 1 MP

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |        |       |         |
|------------|--------|-------|---------|
| Length     | 4 mm   | Width | 11.3 mm |
| Height     | 3 mm   | Depth | 3 mm    |
| Net weight | 0.13 g |       |         |

### General data

|                                   |                            |  |             |
|-----------------------------------|----------------------------|--|-------------|
| Colour                            | Brown                      | Colour of printing                           | White       |
| Material                          | PVC, soft, without Cadmium | Material colour according to resistance code | 1           |
| Operating temperature range, max. | 80 °C                      | Operating temperature range, min.            | -30 °C      |
| Orientation of print              | horizontal                 | Printed characters                           | Numbers     |
| Printing                          | 1                          | Printing method                              | Laser print |
| Recommended industries            | Process, Machinery         | Type of printing                             | Standard    |
| UL 94 flammability rating         | V-0                        |  |             |

### Conductor and cable markers

|                               |                     |                               |                    |
|-------------------------------|---------------------|-------------------------------|--------------------|
| Conductor O.D., max.          | 317 mm              | Conductor O.D., min.          | 10 mm              |
| Conductor cross-section, max. | 500 mm <sup>2</sup> | Conductor cross-section, min. | 16 mm <sup>2</sup> |

### Classifications

|            |             |            |             |
|------------|-------------|------------|-------------|
| ETIM 3.0   | EC001530    | UNSPSC     | 44-12-17-08 |
| eClass 5.1 | 27-14-91-03 | eClass 6.2 | 27-14-91-29 |
| eClass 7.1 | 27-14-91-29 |            |             |

### Approvals

|           |         |
|-----------|---------|
| Approvals |         |
| ROHS      | Conform |

**Datenblatt**

**Cable markers  
CLI M 2-4 BR/WS 1 MP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**



Product is similar to illustration