

Cable glands VG 48-K68

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Screwed joints that comply with the high demands of class of protection IP 68

General ordering data

Type	VG 48-K68
Order No.	1718770000
Version	cable glands, Polyamide 6, RAL 7035, External thread: PG 48
GTIN (EAN)	4008190351977
Qty.	10 pc(s).

Cable glands VG 48-K68

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	69 mm	Net weight	93.8 g
--------	-------	------------	--------

General information

AF size 1	65 mm	Cable gland	PG
Clamping range, max.	44 mm	Clamping range, min.	34 mm
Colour code	RAL 7035	DIN	EN 50262 (for M thread)
External thread	PG 48	Length of thread	14 mm
Material	Polyamide 6	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Seal insert	CR
Torque for cap nut, max.	21 Nm	Torque for cap nut, min.	19 Nm
Torque for connecting adapter, max.	16 Nm	Torque for connecting adapter, min.	12 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 5.1	27-14-91-09	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data	Long-thread version on request, halogen-free without sealing ring
Descriptive text technical data	Version with moulded sealing lip Length L varies depending on the cable diameter used

Approvals

Approvals



ROHS	Conform
------	---------