

Cable glands SKMU EMV PG11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com



Weidmüller has a variety of different cable and wire entry systems in the Portfolio: with different designs of plastic, brass and stainless steel cable glands in the IP66, 67, 68 or IP69k protection classes. As a complete alternative to cable glands, pre-assembled cables with modular multi-wire or multi-cable entry systems can be simply and quickly inserted into electrical equipment. Last but not least, Weidmüller offers EX-certified cable glands and cable/wire entry systems.

- Cable glands made from plastic and brass
- EMC screwed joints
- for areas at risk of explosion
- VDE, CSA and UL approvals

General ordering data

Type	SKMU EMV PG 11
Order No.	1718920000
Version	Cable glands, Locknut, Brass, nickel-plated, PG 11
GTIN (EAN)	4008190352141
Qty.	20 pc(s).

Cable glands SKMU EMV PG11

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 3.85 g

Width

Thickness 1 mm

General information

AF size 1	21 mm	AF size 2	1 mm
Cable gland	PG	Colour code	Miscellaneous
External thread	PG 11	Internal thread	PG 11
Length of thread	4.7 mm	Material	Brass, nickel-plated
O.D.	24.26 mm	Thickness	1 mm

Classifications

ETIM 3.0	EC000940	UNSPSC	30-21-18-01
eClass 5.1	23-11-07-01	eClass 6.2	27-14-91-09
eClass 7.1	27-14-91-09		

Product information

Descriptive text ordering data Further versions on request

Approvals

Approvals
 ROHS Conform

Datenblatt

**Cable glands
SKMU EMV PG11**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Zeichnungen

