

**Z-series, WeiCoS
ZP 2.5/1AN ZA****Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

One terminal strip for the functional unit, one plug-in connector for the cable loom fabrication. All that remains to be done is to clip the two units together during final assembly – just like a plug-in connector. Finished! Whether for railway engineering, mechanical engineering or shipbuilding applications, all are served excellently by the products of the Weidmüller Z-Series. This is because the products are easy to use and practical, and the connections are simple, reliable and quick. Modular and flexible connection systems are especially in demand where complete functional units have to be prefabricated or replaced.

General ordering data

| | |
|------------|---|
| Type | ZP 2.5/1AN ZA |
| Order No. | 1875190000 |
| Version | Z-series, WeiCoS, Plug-in connector, Wemid, Dark Beige, Direct mounting |
| GTIN (EAN) | 4032248500253 |
| Qty. | 50 pc(s). |

Z-series, WeiCoS ZP 2.5/1AN ZA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|--------------------------|-------|------------|-------|
| Length | 23 mm | Height | 41 mm |
| Height of lowest version | 41 mm | Net weight | 3.6 g |

Temperatures

| | | | |
|----------------------------------|--------|----------------------------------|--------|
| Operating temperature | | Storage temperature | |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 120 °C |

Additional technical data

| | | | |
|---------------------|-----------------|------------|--|
| Installation advice | Direct mounting | Open sides | closed |
| Type of mounting | Plugged | Version | Plug, pluggable, With assembly peg, Tension-clamp connection |

Clampable wires (rated connection)

| | | | |
|---|----------------------|---|---------------------|
| Type of connection | Plug-in connection | Stripping length | 10 mm |
| Blade size | 0.6 x 3.5 mm | Connection direction | top |
| Clamping range, rated connection, min. | 0.13 mm ² | Clamping range, rated connection, max. | 4 mm ² |
| Gauge to IEC 60947-1 | A2 | Wire connection cross section, solid core, max. rated connection | 0.5 mm ² |
| Wire connection cross section, solid core max. rated connection | 4 mm ² | Wire connection cross section, finely stranded, max. | 4 mm ² |
| Wire connection cross-section, finely stranded, min. | 0.5 mm ² | Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, min. | 0.5 mm ² |
| Wire connection cross section, finely stranded with wire-end ferrules DIN 46228/1, rated connection, max. | 2.5 mm ² | Wire connection cross section AWG, min. | AWG 26 |
| Wire connection cross section AWG, max. | AWG 12 | | |

Rated data

| | | | |
|---------------------------------|---------------------|---------------|--------------------------|
| Rated cross-section | 2.5 mm ² | Rated voltage | 500 V |
| Rated impulse withstand voltage | 6 kV | Rated current | 24 A |
| Current at maximum wires | 24 A | Standards | IEC 60947-7-1, IEC 61984 |

UL ratings data

| | | | |
|--|--------|--|--------|
| Certificate No. (cURus) | E60693 | Conductor size Factory wiring max. (cURus) | 12 AWG |
| Conductor size Factory wiring min. (cURus) | 26 AWG | Conductor size Field wiring max. (cURus) | 12 AWG |
| Conductor size Field wiring min. (cURus) | 26 AWG | Current size C (cURus) | 20 A |
| Current size D (cURus) | 5 A | Voltage size C (cURus) | 300 V |
| Voltage size D (cURus) | 600 V | | |

Material data

| | | | |
|---------------------------|-------|----------|-------|
| Insulating material | Wemid | Material | Wemid |
| UL 94 flammability rating | V-0 | | |

Datenblatt

**Z-series, WeiCoS
ZP 2.5/1AN ZA**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

System specifications

| | | | |
|--------------------------|------------------|-----------------------------------|--------------------|
| Product family | Z-series, WeiCoS | Type of connection | Plug-in connection |
| Connection direction | top | Levels cross-connected internally | No |
| End cover plate required | No | | |

Classifications

| | | | |
|------------|-------------|------------|-------------|
| UNSPSC | 30-21-18-01 | eClass 6.2 | 27-14-92-14 |
| eClass 7.1 | 27-14-03-05 | | |

Product information

Descriptive text technical data The assessment of the terminal points is carried out according to DIN EN 60999-1. Please observe the rated voltage and current-carrying capacity of the base terminals.

Approvals

Approvals



ROHS Conform