


## OMNIMATE Signal - series LSF LSF-SMT 5.00/15/135 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



PCB terminal for fully automatic assembly in reflow soldering (SMT), with Push In conductor connection system. Conductor inserted and slider operated in same direction (TOP). Packed in box or as tape on reel. Pin lengths optimised at 1.5 mm or 3.5 mm.

- 0.20 - 1.5 mm<sup>2</sup> (IEC) / 24 - 16 AWG (UL)
- 500 V (IEC) / 300 V (UL)
- 17.5 A (IEC) / 12 A (UL)

### General ordering data

|              |  |
|--------------|--|
| Type         | LSF-SMT 5.00/15/135 3.5SN BK TU  |
| Order No.    | <a href="#">1884510000</a>   |
| Version      | PCB terminal, 5.00 mm, No. of poles: 15, 135°, Solder pin length (l): 3.5 mm, tinned, Black, PUSH IN spring connection, Clamping range, rated connection, max.: 1.5 mm <sup>2</sup> , Tube |
| GTIN (EAN)   | 4032248488803  |
| Qty.         | 7 pc(s).   |
| Product data | IEC: 500 V / 17.5 A / 0.2 - 1.5 mm <sup>2</sup><br>UL: 300 V / 12 A / AWG 24 - AWG 16  |
| Packaging    | Tube   |

Erstellungs-Datum January 16, 2014 12:30:38 PM CET

## OMNIMATE Signal - series LSF LSF-SMT 5.00/15/135 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 17.23 g

### System characteristics

|  |                              |  |                           |
|--|------------------------------|--|---------------------------|
| Product family                               | OMNIMATE Signal - series LSF | Wire connection method                     | PUSH IN spring connection |
| Mounting onto the PCB                        | Reflow solder connection     | Conductor outlet direction                 | 135°                      |
| Pitch in mm (P)                              | 5 mm                         | Pitch in inches (P)                        | 0.197 inch                |
| No. of poles                                 | 15                           | Fitted by customer                         | Yes                       |
| Solder pin length (l)                        | 3.5 mm                       | Solder eyelet hole diameter (D)            | 1.1 mm                    |
| Solder eyelet hole diameter tolerance (D)    | + 0,1 mm                     | Number of solder pins per pole             | 2                         |
| Stripping length                             | 8 mm                         | L1 in mm                                   | 70 mm                     |
| L1 in inches                                 | 2.756 inch                   | Touch-safe protection acc. to DIN VDE 0470 | IP 20                     |
| Touch-safe protection acc. to DIN VDE 57 106 | Safe from finger touch       |  |                           |

### Material data

|                           |        |                 |        |
|---------------------------|--------|-----------------|--------|
| Insulating material       | LCP GF | Colour          | Black  |
| UL 94 flammability rating | V-0    | CTI             | ≥ 175  |
| Contact material          | Cu-Leg | Contact surface | tinned |
| Contact base material     | Cu-Leg |                 |        |

### Connectable conductors

|   |                      |   |                      |
|---|----------------------|---|----------------------|
| Clamping range, rated connection, min.          | 0.13 mm <sup>2</sup> | Clamping range, rated connection, max.          | 1.5 mm <sup>2</sup>  |
| Wire connection cross section AWG, min.         | AWG 24               | Wire connection cross section AWG, max.         | AWG 16               |
| Solid, min. H05(07) V-U                         | 0.2 mm <sup>2</sup>  | Solid, max. H05(07) V-U                         | 1.5 mm <sup>2</sup>  |
| Flexible, min. H05(07) V-K                      | 0.2 mm <sup>2</sup>  | Flexible, max. H05(07) V-K                      | 1.5 mm <sup>2</sup>  |
| w. wire end ferrule, DIN 46228 pt 1, min.       | 0.25 mm <sup>2</sup> | w. wire end ferrule, DIN 46228 pt 1, max.       | 1.5 mm <sup>2</sup>  |
| w. plastic collar ferrule, DIN 46228 pt 4, min. | 0.25 mm <sup>2</sup> | w. plastic collar ferrule, DIN 46228 pt 4, max. | 0.75 mm <sup>2</sup> |

### DIN IEC rating data

|  |                  |  |        |
|--|------------------|--|--------|
| Rated current, min. no. of poles (Tu=20°C)                           | 17.5 A           | Rated current, max. no. of poles (Tu=20°C)                               | 17.5 A |
| Rated current, number of poles (Tu=40°C), min                        | 17.5 A           | Rated current, number of poles (Tu=40°C), max.                           | 15 A   |
| Rated voltage for surge voltage class pollution degree II/2          | 500 V            | Rated voltage for surge voltage class pollution degree III/2             | 320 V  |
| Rated voltage for surge voltage class pollution degree III/3         | 250 V            | Rated impulse voltage for surge voltage class pollution degree II/2      | 4 kV   |
| Rated impulse voltage for surge voltage class pollution degree III/2 | 4 kV             | Rated impulse voltage for surge voltage class contamination degree III/3 | 4 kV   |
| Short-time withstand current resistance                              | 3 x 1s with 80 A |  |        |

## OMNIMATE Signal - series LSF LSF-SMT 5.00/15/135 3.5SN BK TU

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

## Technische Daten

### CSA rating data

Institute (CSA)



Rated voltage (Use group B)

300 V

Rated current (use group B) 10 A

Rated voltage (use group D) 300 V

Rated current (use group D) 10 A

Wire cross-section, AWG, min. AWG 24

Wire cross-section, AWG, max. AWG 16

### UL 1059 rating data

Rated voltage (use group B) 300 V

Rated current (use group B) 12 A

Rated voltage (use group D) 300 V

Rated current (use group D) 10 A

Wire cross-section, AWG, min. AWG 24

Wire cross-section, AWG, max. AWG 16

### Classifications

ETIM 3.0

EC001284

UNSPSC

30-21-18-11

eClass 5.1

27-26-11-01

eClass 6.2

27-26-11-01

eClass 7.1

27-44-04-01

### Notes

Notes

- Additional push button colours on request
- Rated current related to rated cross-section & min. No. of poles.
- Wire end ferrule without plastic collar to DIN 46228/1
- P on drawing = pitch
- Operating force of slider max. 40 N
- Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
- Crimping shape "A" for wire end ferrules with PZ 6/5 crimping tool are recommended for the largest cable sizes.

### Approvals

Approvals




ROHS

Conform


**OMNIMATE Signal - series LSF**  
**LSF-SMT 5.00/15/135 3.5SN BK TU**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Zeichnungen**




LSF-SMT 5.00/./135 1.5



LSF-SMT 5.00/./135 1.5



LSF-SMT 5.00/./135 3.5



LSF-SMT 5.00/./135 3.5

