

# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



PCB terminal block, Nominal current: 24 A, Nom. voltage: 320 V, Pitch: 5 mm, Number of positions: 3, Connection method: Screw connection, Mounting: Soldering, Conductor/PCB connection direction: 0°, Color: light gray, Article with lateral pin exit

## Product Features

- PCB terminal block for ME/ME MAX electronics housing
- 5 mm pitch
- PCB terminal block orthogonal to the PCB

## Key commercial data

<b>package_quantity</b>	250
<b>GTIN</b>	4017918459017

## Technical data

### Dimensions

<b>Length</b>	15.3 mm
<b>Pitch</b>	5 mm
<b>Dimension a</b>	10 mm
<b>Pin dimensions</b>	0,8 x 1
<b>Hole diameter</b>	1.4 mm

### General

<b>Range of articles</b>	MKDSO 2,5/..-R
<b>Insulating material group</b>	I
<b>Rated surge voltage (III/3)</b>	4 kV
<b>Rated surge voltage (III/2)</b>	4 kV
<b>Rated surge voltage (II/2)</b>	4 kV
<b>Rated voltage (III/3)</b>	250 V
<b>Rated voltage (III/2)</b>	320 V
<b>Rated voltage (II/2)</b>	630 V
<b>Connection in acc. with standard</b>	EN-VDE
<b>Nominal current I<sub>N</sub></b>	24 A
<b>Nominal cross section</b>	2.5 mm <sup>2</sup>
<b>Maximum load current</b>	24 A
<b>Insulating material</b>	PA
<b>Inflammability class according to UL 94</b>	V0

# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

## Technical data

### General

Internal cylindrical gage	A 2
Stripping length	8 mm
Number of positions	3
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

### Connection data

Conductor cross section solid min.	0.14 mm <sup>2</sup>
Conductor cross section solid max.	2.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.14 mm <sup>2</sup>
Conductor cross section stranded max.	2.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	26
Conductor cross section AWG/kcmil max	14
2 conductors with same cross section, solid min.	0.14 mm <sup>2</sup>
2 conductors with same cross section, solid max.	0.75 mm <sup>2</sup>
2 conductors with same cross section, stranded min.	0.14 mm <sup>2</sup>
2 conductors with same cross section, stranded max.	0.75 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.25 mm <sup>2</sup>
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	0.75 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm <sup>2</sup>
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	1.5 mm <sup>2</sup>
Minimum AWG according to UL/CUL	30
Maximum AWG according to UL/CUL	12

## classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27141190
eCl@ss 6.0	27141190
eCl@ss 7.0	27141190
eCl@ss 8.0	27141190

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC002643

# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

## classifications

### ETIM

<b>ETIM 5.0</b>	EC002643
-----------------	----------

### UNSPSC

<b>UNSPSC 6.01</b>	31261501
<b>UNSPSC 7.0901</b>	31261501
<b>UNSPSC 11</b>	31261501
<b>UNSPSC 12.01</b>	31261501
<b>UNSPSC 13.2</b>	31261501

## approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / GOST / CCA / IEC/IEE CB Scheme / GOST / cULus Recognized /

### Approval details

Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	10 A	10 A
mm <sup>2</sup> /AWG/kcmil	28-12	28-12

Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	10 A
mm <sup>2</sup> /AWG/kcmil	30-12	30-12

Nominal voltage UN	450 V
Nominal current IN	24 A
mm <sup>2</sup> /AWG/kcmil	0.2-2.5

--	--

# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

## approvals

Usegroups	B	D
Nominal voltage UN	300 V	300 V
Nominal current IN	20 A	10 A
mm <sup>2</sup> /AWG/kcmil	30-12	30-12

GOST

CCA	
Nominal voltage UN	450 V
Nominal current IN	24 A
mm <sup>2</sup> /AWG/kcmil	2.5


IECEE CB Scheme	
Nominal voltage UN	450 V
Nominal current IN	24 A
mm <sup>2</sup> /AWG/kcmil	2.5

cULus Recognized

## Drawings


# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

Drilling diagram




# PCB terminal block - MKDSO 2,5/ 3-R KMGY - 2854092

Dimensioned drawing



Schematic diagram



Pin assignment right

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>