

# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



PCB terminal block, Nominal current: 2 A, Nom. voltage: 250 V, Pitch: 3.5 mm, Number of positions: 3, Connection method: Spring-cage conn., Mounting: Soldering, Conductor/PCB connection direction: 45 °, Color: green, Soldering legs in front area, one-rowed

The figure shows a 10-position version of the product

## Product Features

- 3.5 mm pitch
- Compact design with easy actuation and direct plug-in technology
- Dielectric strength and mechanical stability increased thanks to zigzag pinning. Pinning always starts at the front right position. Special pinning versions are available on request.
- Color coding and mixed pitches as an option

## Key commercial data

<b>package_quantity</b>	250
<b>GTIN</b>	4017918922054

## Technical data

### Dimensions

<b>Length</b>	12 mm
<b>Height</b>	13.1 mm
<b>Pitch</b>	3.5 mm
<b>Dimension a</b>	7 mm
<b>Pin dimensions</b>	0,4 x 0,75 mm
<b>Pin spacing</b>	3.5 mm
<b>Hole diameter</b>	1 mm

### General

<b>Range of articles</b>	PTSA 1,5
<b>Insulating material group</b>	I
<b>Rated surge voltage (III/3)</b>	2.5 kV
<b>Rated surge voltage (III/2)</b>	2.5 kV
<b>Rated surge voltage (II/2)</b>	2.5 kV
<b>Rated voltage (III/3)</b>	200 V
<b>Rated voltage (III/2)</b>	250 V
<b>Rated voltage (II/2)</b>	400 V
<b>Connection in acc. with standard</b>	EN-VDE

# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976

## Technical data

### General

Nominal current I <sub>N</sub>	2 A
Nominal cross section	1.5 mm <sup>2</sup>
Maximum load current	2 A
Insulating material	PA
Solder pin surface	Sn
Inflammability class according to UL 94	V0
Stripping length	9 mm
Number of positions	3

### Connection data

Conductor cross section solid min.	0.5 mm <sup>2</sup>
Conductor cross section solid max.	1.5 mm <sup>2</sup>
Conductor cross section stranded min.	0.5 mm <sup>2</sup>
Conductor cross section stranded max.	1.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule without plastic sleeve max.	1 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm <sup>2</sup>
Conductor cross section stranded, with ferrule with plastic sleeve max.	0.5 mm <sup>2</sup>
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	16
Minimum AWG according to UL/CUL	24
Maximum AWG according to UL/CUL	16

## classifications

### eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27141109
eCl@ss 5.0	27141190
eCl@ss 5.1	27141190
eCl@ss 6.0	27261101
eCl@ss 7.0	27440401
eCl@ss 8.0	27440401

### ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002643
ETIM 5.0	EC002643

### UNSPSC

UNSPSC 6.01	30211801
-------------	----------

# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976

## classifications


### UNSPSC


<b>UNSPSC 7.0901</b>	39121432
<b>UNSPSC 11</b>	34131203
<b>UNSPSC 12.01</b>	39121432
<b>UNSPSC 13.2</b>	39121432


## approvals

UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / CCA / GOST / GOST / cULus Recognized /

### Approval details

<b>UL Recognized</b> 		
<b>Usegroups</b>	<b>B</b>	<b>D</b>
Nominal voltage UN	300 V	300 V
Nominal current IN	5 A	5 A
mm <sup>2</sup> /AWG/kcmil	24-16	24-16

<b>VDE Gutachten mit Fertigungsüberwachung</b> 	
Nominal voltage UN	130 V
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	0.5-0.75

<b>cUL Recognized</b> 		
<b>Usegroups</b>	<b>B</b>	<b>D</b>
Nominal voltage UN	300 V	300 V
Nominal current IN	5 A	5 A
mm <sup>2</sup> /AWG/kcmil	24-16	24-16

<b>CCA</b>	
Nominal voltage UN	
Nominal current IN	2 A
mm <sup>2</sup> /AWG/kcmil	0.75

# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976


approvals



Drawings

# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976


Drilling diagram



The illustration shows the drilling diagram of the 5-position product version


# Spring-cage PCB terminal block - PTSA 1,5/ 3-3,5-F - 1984976

Diagram



Derating diagram for 5 pins;reduction factor=1

Dimensioned drawing



The illustration shows the dimensional drawing of the 5-position product version

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>