

**Accessories  
DAE M12 SS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com



Pressure-compensation elements ensure good ventilation of the enclosure and prevent the build-up of condensation while maintaining the appropriate IP class of protection.

**General ordering data**

Type	DAE M12 SS
Order No.	<a href="#">1868550000</a>
Version	Compensating element, Stainless steel 1.4305 (303), External thread: M 12, IP 66, IP 68, IP 69K
GTIN (EAN)	4032248440405
Qty.	10 pc(s).

**Datenblatt**

**Accessories  
DAE M12 SS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	21.1 mm	Net weight	15.2 g
--------	---------	------------	--------

**General information**

AF size 1	17 mm	Air flow	0.8 l/min at 0.1 bar ΔP, up to 7.6 l/min at 1bar ΔP
Cable gland	metric	External thread	M 12
Length of thread	10 mm	Material	Stainless steel 1.4305 (303)
O-Ring	NBR	Operating temperature range, max.	105 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Torque for connecting adapter, max.	1.5 Nm	Torque for connecting adapter, min.	1.5 Nm
Wasser inlet point	> 1.5 bar		

**Classifications**

ETIM 3.0	EC000441	UNSPSC	30-21-18-01
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09

**Approvals**

Approvals



ROHS	Conform
------	---------