

Feed-through terminal block - UT 10 YE - 3046294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Feed-through terminal block, Connection method: Screw connection, Cross section: 0.5 mm² - 16 mm², AWG: 20 - 6, Width: 10.2 mm, Color: yellow, Mounting type: NS 35/7,5, NS 35/15

The illustration shows the color version



Key commercial data

package_quantity	50
GTIN	4017918975630

Technical data

General

Number of levels	1
Number of connections	2
Color	yellow
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	76 A (with 16 mm ² conductor cross section)
Rated surge voltage	8 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	76 A
Nominal voltage U _N	1000 V
Open side panel	ja

Dimensions

Width	10.2 mm
Length	47.7 mm
Height NS 35/7,5	47.5 mm
Height NS 35/15	55 mm

Feed-through terminal block - UT 10 YE - 3046294

Technical data

Connection data

Note	Note: Product releases, connection cross sections and notes on connecting aluminum cables can be found in the download area.
Conductor cross section solid min.	0.5 mm ²
Conductor cross section solid max.	16 mm ²
Conductor cross section AWG/kcmil min.	20
Conductor cross section AWG/kcmil max	6
Conductor cross section stranded min.	0.5 mm ²
Conductor cross section stranded max.	16 mm ²
Min. AWG conductor cross section, stranded	20
Max. AWG conductor cross section, stranded	6
Conductor cross section stranded, with ferrule without plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	10 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	0.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	10 mm ²
2 conductors with same cross section, solid min.	0.5 mm ²
2 conductors with same cross section, solid max.	6 mm ²
2 conductors with same cross section, stranded min.	0.5 mm ²
2 conductors with same cross section, stranded max.	6 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	6 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, min.	0.5 mm ²
2 conductors with same cross section, stranded, ferrules without plastic sleeve, max.	2.5 mm ²
Connection method	Screw connection
Stripping length	10 mm
Internal cylindrical gage	A6
Screw thread	M4
Tightening torque, min	1.5 Nm
Tightening torque max	1.8 Nm

classifications

eCl@ss

eCl@ss 4.0	27141120
eCl@ss 4.1	27141120
eCl@ss 5.0	27141120
eCl@ss 5.1	27141120

Feed-through terminal block - UT 10 YE - 3046294

classifications

eCl@ss

eCl@ss 6.0	27141120
eCl@ss 7.0	27141120
eCl@ss 8.0	27141120

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC000897
ETIM 5.0	EC000897

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

IECEX / ATEX / CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / DNV / IECCEB Scheme / GL / cULus Recognized /

Approval details

IECEX	
Nominal voltage UN	690 V
Nominal current IN	54 A
mm ² /AWG/kcmil	0.5-10

ATEX	
Nominal voltage UN	690 V
Nominal current IN	69 A
mm ² /AWG/kcmil	0.5-16

CSA		
Usegroups	B	C
Nominal voltage UN	600 V	600 V

Feed-through terminal block - UT 10 YE - 3046294

approvals

Usegroups	B	C
Nominal current IN	65 A	65 A
mm ² /AWG/kcmil	20-6	20-6

UL Recognized

Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	65 A	65 A
mm ² /AWG/kcmil	20-6	20-6

VDE Gutachten mit Fertigungsüberwachung

Nominal voltage UN	1000 V
Nominal current IN	
mm ² /AWG/kcmil	0.5-10

cUL Recognized

Usegroups	B	C
Nominal voltage UN	600 V	600 V
Nominal current IN	65 A	65 A
mm ² /AWG/kcmil	20-6	20-6

DNV

IECEE CB Scheme

Nominal voltage UN	1000 V
Nominal current IN	
mm ² /AWG/kcmil	0.5-10

GL

cULus Recognized

Feed-through terminal block - UT 10 YE - 3046294

accessories

Pick-off terminal block

AGK 4-UT 10 - 3047112



End cover

D-UT 2,5/10 - 3047028



D-UT 2,5/10 YE - 3047248



Partition plate

ATP-UT - 3047167



Screwdriver tools

SZS 1,0X4,0 VDE - 1205066



Feed-through terminal block - UT 10 YE - 3046294

accessories

Marker pen

X-PEN 0,35 - 0811228



Bridge

FBS 2-10 - 3005947



RB UT 10-(2,5/4) - 3047060



RB UT 10-ST(2,5/4) - 3047086



Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



Feed-through terminal block - UT 10 YE - 3046294

accessories

NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



Feed-through terminal block - UT 10 YE - 3046294

accessories

NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



NS 35/15 PERF 2000MM - 1201730



NS 35/15 UNPERF 2000MM - 1201714



NS 35/15 WH PERF 2000MM - 0806602



Feed-through terminal block - UT 10 YE - 3046294

accessories

NS 35/15 WH UNPERF 2000MM - 1204135



NS 35/15 AL UNPERF 2000MM - 1201756



NS 35/15 ZN PERF 2000MM - 1206599



NS 35/15 ZN UNPERF 2000MM - 1206586



NS 35/15 CU UNPERF 2000MM - 1201895



NS 35/15 CAP - 1206573



Feed-through terminal block - UT 10 YE - 3046294

accessories

NS 35/15-2,3 UNPERF 2000MM - 1201798



Terminal marking

ZB 10:UNBEDRUCKT - 1053001



UC-TM 10 - 0818069



UCT-TM 10 - 0829142



TMT 10 R - 0816210



Labeled terminal marker

Feed-through terminal block - UT 10 YE - 3046294

accessories

ZB 10 CUS - 0824941



UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



TMT 10 R CUS - 0824500



Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>