


Type Designation 4106
 Designation IEC LR6
 System Zn-MnO₂ (Alkaline)
 Shelf Life (Coding) 5 years
 (In consideration of typical loss o)
 Nominal Voltage [V] 1.5
 Typical Capacity C [mAh] 2700 (discharge with high-resistance)
 Permissible Temperature Range - 10 °C ... 50 °C
 Weight, approx. [g] 23
 Volume [ccm] 7.62

Dimensions [mm]	min:	max:
Ø	13.5	14.5
A	-	50.5
B	49.2	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-


Discharge Type:
1 H/D, 7 D/W Motor / Toy

Load: 3.9 Ohm




Discharge Type:
4 H/D, 7 D/W Radio


Load: 43 Ohm



Discharge Type:
1 H/D, 7 D/W Personal cassette player and tape recorder

Load: 10 Ohm






Type Designation	4706
Designation IEC	LR6
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)	7 years
(In consideration of typical loss o)	
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	2900 (discharge with high-resistance)
Permissible Temperature Range	- 20 °C ... 50 °C
Weight, approx. [g]	24
Volume [ccm]	7.69

Dimensions [mm]	min:	max:
Ø	13.5	14.5
A	-	50.5
B	49.5	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-


Discharge Type:
10 S/M, 1 H/D, 7 D/W
Photo Flash


Load: 1000 mA



Discharge Type:
2 S/28 S, 5 M/H
Digital Still Camera

Load: 1500 mW / 650 mW





Type Designation	4906
Designation IEC	LR6
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)	5 years
(In consideration of typical loss o)	
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	2900 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	24
Volume [ccm]	7.69

Dimensions [mm]	min:	max:
Ø	13.5	14.5
A	-	50.5
B	49.5	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-

Discharge Type:
1 H/D, 7 D/W Motor / Toy

Load: 3.9 Ohm

Discharge Type:
4 H/D, 7 D/W Radio

Load: 43 Ohm

Discharge Type:
1 H/D, 7 D/W Personal Cassette Player and Tape Recorder

Load: 10 Ohm