

## Test Verification of Conformity

On the basis of the referenced test report(s), the sample(s) of the below product has been found to comply with the relevant harmonized standard(s) to the directive(s) listed on this verification at the time the tests were carried out.

The manufacturer may indicate compliance to said directive(s) by signing a DoC himself and applying the CE-marking to products identical to the tested sample(s). In addition, the manufacturer shall file and keep the documentation according to the rules of the applicable directive(s) and shall consider changes of the standard(s) if relevant. Additional requirements may be applicable such as additional directives or local laws.


**Applicant Name & Address** : Everflourish Electrical Co.,Ltd.  
Renjiu Village Wuxiang Town, Yinzhou Ningbo, 315111,  
P.R.China.

**Manufacturer Name & Address** : Same as applicant

**Product(s) Tested** : Multiple socket outlet with cord extension set

**Ratings and principal characteristics** : 16A, 230Vac, IP20, Class I, non-rewirable, with 6-ways  
DIN49440-1 socket-outlets with shutters, with remote  
control switch, with a transmitter, with a non-rewirable plug  
with cord H05VV-F 3G1,5mm<sup>2</sup> (The min 1,4m in length for  
3G1,5mm<sup>2</sup>).

**Model(s)** : EMP306RF(Receiver); EMW500T(Transmitter)

**Brand name** :  EVERFLOURISH

**Relevant Standard(s) / Specification(s) / Directive(s)** : DIN VDE 0620-1:2005-04 + EK1/08-370:2008  
EN 61058-1:2002 + A2:2008  
the Low Voltage Directive 2006/95/EC


**Verification Issuing Office Name & Address** : Intertek Testing Services Shanghai  
Building No.86, 1198 Qinzhou Road (North), Shanghai  
200233, China

**Verification Number** : SH08030740-V1

**Report Number(s)** : SH08030740-001  
SH08030740-002

**NOTE 1:** This verification is part of the full test report(s) and should be read in conjunction with it.

This Verification is for the exclusive use of Intertek's Client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party other than to the Client in accordance with the agreement for any loss, expense or damage occasioned by the use of this Verification. Only the Client is authorized to copy or distribute this Verification. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test results referenced from this Verification are relevant only to the sample tested. This Verification by itself does not imply that the material, product or service is or has ever been under an Intertek certification program.



Leo Shi  
Manager  
28 August 2008



Handled by  
Elyn Jiang  
Direct telephone  
+86 21 61278350  
E-mail  
Shanghai-LC@intertek.com  
Your Reference  
SH08030740-002

27 August 2008

Dear Sir/Madam,

We are pleased to enclose your Intertek S Mark Certificate (No 811945).

**The S Mark – a marketing resource**

S Mark Certification is a way of making sure that your brand's equity will not be put at risk by a safety failure of the product. The use of the S Mark in your marketing is also a way of adding value to your brand and promoting trust among your customers.

The S Mark is a European safety mark offered by Intertek ETL SEMKO. The letter 'S' tells 450 million people in Europe that your product is safe. The word for safety starts with an 'S' in most of the languages in Europe, e.g. Safety, Sicherheit, Seguridad, Sécurité, Sicurezza, and Säkerhet.

As products become increasingly interchangeable, trust counts more than ever. This is why the S Mark is a key selling point. It is a well known symbol for safety and shows that Intertek has independently tested and certified the product's compliance to applicable European safety requirements. Critical consumers and retailers look for third-party validation to complement their CE marking, as it helps retailers to meet their product liability requirements, and make the consumers' buying process simpler.



**Mandatory factory inspections**

In addition to your product certification, it is mandatory for inspections to be performed at your manufacturing site/s. The inspections are carried out by our inspectors or subcontractors. For details of the technical requirements for these inspections, please contact [inspection.etlsemko@intertek.com](mailto:inspection.etlsemko@intertek.com).

Yours sincerely

Local Certification Manager  
Wolfram Zeitz

Enclosure: S Mark Certificate

# Certificate



for European Product Safety

Reference No. 811945

## Multiple socket outlet with cord extension set

Type designation EMP306RF (Receiver), EMW500T (Transmitter)

Certificate holder **Everflourish Electrical Co.,Ltd.  
Renjiu Village Wuxiang Town,  
Yinzhou Ningbo, 315111,  
P.R. China**

The product complies with the standard(s) IEC 60884-1: 2002  
EN 61058-1: 2002+A2:2008  
SS 428 0834: 2004  
SFS 5610: 2004  
SB 107-2-D1 4ed  
NEK 502: 2006

Date of expiry 27 August 2013


EU Directive information *The product satisfies the provisions for CE marking according to the Low Voltage Directive 2006/95/EC.*

Additional information in Appendix

Certification Body Intertek Semko AB, Product Certification

Place Shanghai

Signed

  
\_\_\_\_\_  
Wolfram Zeitz

Date 27 August 2008


Page 1 of 2



## Appendix

Reference No. 811945

### Technical data

Type designation	EMP306RF(Receiver), EMW500T(Transmitter)
Rated Voltage (V)	230~
Rated Current (A)	16
IP-Class	20
Class	I
Type of Cord	H05VV-F 3G1,5mm <sup>2</sup>
Number of Conductors	3
Standard Sheet:	CEE7 / III
BRAND Name:	 <b>EVERFLOURISH</b>

### Product information

Non-rewirable, with 6-ways socket-outlets with shutters, with remote control switch, with a transmitter, with a non-rewirable plug.

### Manufacturing site(s)

Everflourish Electrical Co ,Ltd.  
Renjiu Village Wuxiang Town,  
Yinzhou Ningbo, 315111,  
P R. China

This certificate, which includes production control, is considered to constitute sufficient support for an EC Declaration of Conformity and CE marking of the product according to the Low Voltage Directive 2006/95/EC

### Certification Body

Intertek Semko AB, Product Certification

Place Shanghai

### Signed

  
\_\_\_\_\_  
Wolfram Zeitz

Date 27 August 2008

*This Certificate is for the exclusive use of Intertek's Client and is provided pursuant to the Certification agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this certificate. Only the Client is authorized to permit copying or distribution of this certificate and then only in its entirety. Use of Intertek's Certification mark is restricted to the conditions laid out in the agreement. Any further use of the Intertek name for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. Initial Factory Assessments and Follow up Services are for the purpose of assuring appropriate usage of the Certification mark in accordance with the agreement, they are not for the purposes of production quality control and do not relieve the Client of their obligations in this respect.*

## Certificate



## Prüfbescheinigung nach dem Geräte- und Produktsicherheitsgesetz

Test Certificate in compliance with the Equipment and Product Safety Law

Bescheinigungs-Nr. (Certificate No.): 08SHN2419-01

Das Produkt entspricht den Rechtsverordnungen zum Geräte- und Produktsicherheitsgesetz (GPSG) bzw. den derzeit anerkannten Regeln der Technik und erfüllt §7 des GPSG.

(The designated product above is in compliance with the judicial requirements of the Equipment and Product Safety Law (GPSG) or the currently accepted rules of technology and complies with §7 of the GPSG.)

*Bescheinigungsinhaber (Certificate Holder)*

Everflourish Electrical Co., Ltd.  
Renjiu Village Wuxiang Town  
Yinzhou, Ningbo 315111  
P. R. China

*Markenname (Brandname)*

Everflourish (logo)

*Fertigungsstätte (Manufacturing Site)*

Everflourish Electrical Co., Ltd.  
Renjiu Village Wuxiang Town  
Yinzhou, Ningbo 315111  
P. R. China

*Produkt (Product)*

Mehrfachsteckdose mit Verlängerungskabel  
Multiple socket outlet with cord extension set

*Typbezeichnung (Type)*

EMP306RF(Receiver), EMW500T(Transmitter)

*Beschreibung (Description)*

16A, 230Vac, IP20, Schutzklasse I (Class I), nicht wiederanschließbar, mit 6-Fach DIN49440-1 Steckdose, mit Kindersicherung, mit Funkferngesteuerter Schalter, mit einem Sender EMW500T, mit nicht wiederanschließbarem Stecker, mit Kabel H05RR-F 3G1,5mm<sup>2</sup> (min Länge 1,4m).  
(non-rewirable, with 6-ways DIN49440-1 socket-outlets with shutters, with remote control switch, with a transmitter type EMW500T, with a non-rewirable plug with cord H05VV-F 3G1,5mm<sup>2</sup> (The min 1,4m in length for 3G1,5mm<sup>2</sup>))

*Prüfbericht-Nr. (Test Report No.)*

SH08030740-001

SH08030740-002

Einzelheiten siehe Anhang (Details see attachment)

*Geprüft nach (Tested according to)*

EN 61058-1:2002+A2:08


DIN VDE 0620-1:2005 + EK1/08-370:2008

*Gültig bis (valid until)*

2013-08-27

*Erstellt am (Issued on)*

2008-08-27



Intertek Deutschland GmbH  
Dipl.-Ing. (FH) Wolfram Zeitz

Dem Zertifikat liegen die Allgemeinen Geschäftsbedingungen der Intertek Deutschland GmbH zu Grunde. Bitte beachten Sie die umseitigen Hinweise  
The General Business Conditions of Intertek Deutschland GmbH is an integral part of this certificate. Please also refer to the information overleaf.

Intertek Deutschland GmbH, Nikolaus-Otto-Str. 13, 70771 Leinfelden-Echterdingen


Sitz Leinfelden-Echterdingen, Registergericht Stuttgart, HRB Nr. 225262, Geschäftsführer: Andreas Ehrhardt  
Tel: +49 711 27311-0 Fax: +49 711 27311-559 E-Mail: gs@intertek.com web: www.intertek.de

### Constructional Data Form (CDF)

<i>Certificate Holder:</i>	Everflourish Electrical Co., Ltd. Renjiu Village Wuxiang Town Yinzhou, Ningbo 315111 P. R. China
<i>Manufacturing Site:</i>	Everflourish Electrical Co., Ltd. Renjiu Village Wuxiang Town Yinzhou, Ningbo 315111 P. R. China
<i>Product: (in German)</i>	Mehrfachsteckdose mit Verlängerungskabel
<i>Product: (in English)</i>	Multiple socket outlet with cord extension set
<i>Type:</i>	EMP306RF(Receiver), EMW500T(Transmitter)
<i>Brandname:</i>	Everflourish (logo)
<i>Description:</i>	16A, 230Vac, IP20, Class I, non-rewirable, with 6-ways DIN49440-1 socket-outlets with shutters, with remote control switch, with a transmitter type EMW500T, with a non-rewirable plug with cord H05VV-F 3G1,5mm <sup>2</sup> (The min 1,4m in length for 3G1,5mm <sup>2</sup> ).
<i>Test Report No :</i>	SH08030740-001:2008-08-12 SH08030740-002:2008-08-12
<i>Tested according to:</i>	EN 61058-1:2002+A2:08 DIN VDE 0620-1:2005 + EK1/08-370:2008
<i>Valid until:</i>	2013-08-27
<i>Issued on:</i>	2008-08-27

**Product Information:**


<p><b>General product information</b></p> <p>With remote control switch</p>
---



Copy of marking plate



Product Pictures



List of Critical Components

Object / part No.	Manufacturer/ trademark <sup>2)</sup>	Type / model <sup>2)</sup>	Technical data	Standard	Mark(s) of conformity <sup>1)</sup>
Non-rewirable plug with cord	Ningbo Linsheng	LA017A	DIN 49441-R2, 16A 250V~, with cord H05VV-F 3G1,5mm <sup>2</sup>	DIN VDE 0620- 1:2005	VDE: 40005774
Non-rewirable plug with cord, alternative	Yuyao Kaifeng	KF-CR2	Same as above	DIN VDE 0620- 1:2005	VDE: 40008190
Non-rewirable plug with cord, alternative	Yuyao Yuxiang	YXD-03A	Same as above	DIN VDE 0620- 1:2005	VDE: 40010269
PCB integrated remote control switch	Everflourish Electrical Co.,Ltd.	-	-	EN 61058- 1:2002+A2:2008	Ref. Report No.: SH08030740-002
Relay	Zhejiang HKE Relay Co., Ltd.	HCP3-S- DC12V-A	16A 250VAC	EN 61810-1:2004	TÜV No: R50097843
Capacitor	Sichuan Zhongxing Electr. Co., Ltd.	MKP61	X2, 1,0µF, 275VAC	EN 132400: 1994+A2:98+A3:9 8+A4:01	VDE: 40000990
Capacitor, alternative	various	various	Same as above	Same as above	S and other EU certification marks
PCB	GALAXY Electronics	01V0 (E157634)	94V-0, Min thickness 0.65mm, 130°C	EN 61058-1:2002	Test with appliance
PCB, alternative	various	various	Same as above	Same as above	S, ETL, UL and other EU certification marks
Internal wire	Zhejiang Xinya	-	16AWG, 105°C, 600V	EN 61058-1:2002	UL: E170689
Internal wire, alternative	Ningbo Riyue	-	Same as above	EN 61058-1:2002	UL: E319451



Attachment to Certificate No.: 08SHN2419-01


Object / part No.	Manufacturer/ trademark <sup>2)</sup>	Type / model <sup>2)</sup>	Technical data	Standard	Mark(s) of conformity <sup>1)</sup>
Enclosure Live parts carrier (white)	Ningbo International trade Co., Ltd.	-	PP, Min thickness 1,5mm	DIN VDE 0620- 1:2005	Test with appliance
Shutters (black, red, green, blue, white)	Ningbo International trade Co., Ltd.	-	PA66, Min thickness 3,5mm (refer to the shutter's drawing)	DIN VDE 0620- 1:2005	Test with appliance

<sup>1)</sup> An asterisk indicates a mark which assures the agreed level of surveillance  
<sup>2)</sup> "Various" means any type from any manufacturer that complies with the specification can be used.

Modification Summary

The following changes have been made to this CDF:

Date	Local Project no.	Description of Change
None	None	None



Signed

W. Zeitz  
Dipl.-Ing (FH) Wolfram Zeitz

Date 2008-08-27