


Accessories
SSCH 10X3X1000 CU/SN**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

In the switching facilities and controllers, the N conductor may need to be merged with the PE conductor at a central point. For this reason, busbars are available that allow a wide range of cables to be connected within a confined space (up to 70 wires on one metre of rail). The cables are connected via a compression piece or a clamping yoke. For the first variant there is no need to bend the lugs. A guide lug at the compression piece grips into the busbar and holds tightly to the compression piece. The clamping yokes can be moved on the busbar and adjusted to the whole wiring in the facility. The busbar can be used without holes in various lengths. The rail holding clamp SH is used for fastening. On longer rails, it can also be aligned between clamping yokes.

General ordering data

Type	SSCH 10X3X1000 CU/SN
Order No.	034890000
Version	Accessories, Busbar, Copper, 1000 mm
GTIN (EAN)	4008190024802
Qty.	1 m

Accessories SSCH 10X3X1000 CU/SN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technische Daten

Dimensions and weights

Length	1,000 mm	Width	10 mm
Height	3 mm	Net weight	267 g

Temperatures

Operating temperature	Storage temperature
-----------------------	---------------------

Additional technical data

Installation advice	Version	15 x 6 mm busbar connection
Direct mounting		

Rated data

Rated current	140 A
---------------	-------

Material data

Surface finish	galvanized	Material	Copper
Colour	Silver		

System specifications

Product family	Accessories
----------------	-------------

Classifications

ETIM 3.0	EC000485	UNSPSC	30-21-18-01
eClass 5.1	27-14-06-04	eClass 6.2	27-40-06-06
eClass 7.1	27-14-92-14		

Approvals

Approvals	
ROHS	Conform