

Classic (LR03)


AAA



Specifications


Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	IEC-LR03
Nominal Voltage:	1.5 volts
Operating Temp:	-18°C to 55°C
Typical Weight:	11.5 grams
Typical Volume:	(0.2 cubic inch)
Jacket:	Plastic Label
Shelf Life:	7 years at 21°C (80% of initial capacity)
Terminal:	Flat Contact

Industry Standard Dimensions



Performance Comparison


Classic vs. Typical Carbon Zinc (AAA) at 21°C



Device Selection Guide:

- Photoflash
- Games, Digital Audio
- Lighting
- Remote Control
- Radio

Battery Selection Indicator



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.