

# Round cable - VIP-CAB-FLK20/FR/OE/0,14/1,5M - 2900141

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Assembled round cable with a 20-pos. molded socket strip (90° output) and an open end. On the open end, the wires are labeled with 1 to 20 and have ferrules, cable length: 1.5 m

The figure shows the 14-pos. version

## Product Features

- 20 and 50-pos.
- Connector according to IEC 60603-13
- Open end at one end
- 1:1 connection

## Key commercial data

package_quantity	1
GTIN	4046356476959

## Technical data

### General

Nominal voltage $U_N$	< 50 V AC
Nominal voltage $U_N$	60 V DC
Max. current carrying capacity per path	1 A
Max. conductor resistance	0.16 $\Omega/m$
Length of cable	1.5 m
Single wire, cross section	0.14 mm <sup>2</sup>
AWG	26
Conductor construction: Number of litz wires:	7
Single wire, material	Cu tin-plated
External diameter	7.6 mm
Cable, preassembly	Insulation displacement, IEC 60352-4/DIN EN 60352-4
Shielding	no

### Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

# Round cable - VIP-CAB-FLK20/FR/OE/0,14/1,5M - 2900141

## Technical data

### Connector, module side

<b>Number of positions</b>	20
<b>Connectors</b>	IDC/FLK socket strip (2.54 mm)
<b>Number of plugs</b>	1

### Connector, controller side

<b>Number of positions</b>	20
<b>Connectors</b>	Open end
<b>Number of plugs</b>	0

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27060306
<b>eCl@ss 4.1</b>	27060306
<b>eCl@ss 5.0</b>	27061801
<b>eCl@ss 5.1</b>	27061801
<b>eCl@ss 6.0</b>	27061801
<b>eCl@ss 7.0</b>	27061801
<b>eCl@ss 8.0</b>	27061801

### ETIM

<b>ETIM 2.0</b>	EC000237
<b>ETIM 3.0</b>	EC000237
<b>ETIM 4.0</b>	EC000237
<b>ETIM 5.0</b>	EC000237

### UNSPSC

<b>UNSPSC 6.01</b>	26121620
<b>UNSPSC 7.0901</b>	26121620
<b>UNSPSC 11</b>	26121620
<b>UNSPSC 12.01</b>	26121620
<b>UNSPSC 13.2</b>	26121620

## Drawings