

Installation level terminal block - STN 16 - 3038286

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Installation level terminal block, Spring-cage connection, Cross section: 0.2 mm² - 25 mm², AWG: 24 - 4, Width: 12 mm, Color: blue, Mounting type: NS 35/15, NS 35/7,5

Product Features

- ☑ The N disconnect slides are located in the same position on all Phoenix Contact screw and spring-cage installation terminal blocks

Key commercial data

package_quantity	25
GTIN	4017918899783

Technical data

General

Note	Assembly instructions:For secure fastening of the neutral busbar, supports must be set at the beginning and end of each terminal strip as well as every 20 cm on longer terminal strips.
Number of levels	1
Number of connections	2
Color	blue
Insulating material	PA
Inflammability class according to UL 94	V0

General

Maximum load current	76 A (with 25 mm ² conductor cross section)
Current carrying capacity of the neutral busbar	140 A
Rated surge voltage	6 kV
Pollution degree	3
Surge voltage category	III
Insulating material group	I
Connection in acc. with standard	IEC 60947-7-1
Nominal current I _N	76 A
Nominal voltage U _N	400 V
Open side panel	ja

Dimensions

Width	12 mm
Length	95 mm

Installation level terminal block - STN 16 - 3038286

Technical data

Dimensions

Height NS 35/7,5	50 mm
Height NS 35/15	57.5 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	25 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	16 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	4
Conductor cross section stranded, with ferrule without plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule without plastic sleeve max.	16 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve min.	1.5 mm ²
Conductor cross section stranded, with ferrule with plastic sleeve max.	16 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, min.	1.5 mm ²
2 conductors with same cross section, stranded, TWIN ferrules with plastic sleeve, max.	4 mm ²
Connection method	Spring-cage connection
Stripping length	18 mm
Internal cylindrical gage	A7

classifications

eCl@ss

eCl@ss 4.0	27141125
eCl@ss 4.1	27141125
eCl@ss 5.0	27141125
eCl@ss 5.1	27141125
eCl@ss 6.0	27141125
eCl@ss 7.0	27141125
eCl@ss 8.0	27141125

ETIM

ETIM 2.0	EC001329
ETIM 3.0	EC001329
ETIM 4.0	EC001329
ETIM 5.0	EC001329

UNSPSC

UNSPSC 6.01	30211811
-------------	----------

Installation level terminal block - STN 16 - 3038286

classifications


UNSPSC

UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

approvals

GOST / GOST /

Approval details



accessories

Cover profile

AP-NLS - 5037133



Screwdriver tools

SZF 3-1,0X5,5 - 1206612



End cover

Installation level terminal block - STN 16 - 3038286

accessories

D-STI 10/16 - 3038309



Support

AB-STI 16/10 - 3037669



Documentation

ST-IL - 3039900



Bridge

FBS 2-12 - 3005950



Neutral conductor rail

NLS-CU 3/10 SN 1000MM - 0402174



Installation level terminal block - STN 16 - 3038286

accessories

Mounting rail

NS 35/ 7,5 PERF 2000MM - 0801733



NS 35/ 7,5 UNPERF 2000MM - 0801681



NS 35/ 7,5 WH PERF 2000MM - 1204119



NS 35/ 7,5 WH UNPERF 2000MM - 1204122



NS 35/ 7,5 AL UNPERF 2000MM - 0801704



Installation level terminal block - STN 16 - 3038286

accessories

NS 35/ 7,5 ZN PERF 2000MM - 1206421



NS 35/ 7,5 ZN UNPERF 2000MM - 1206434



NS 35/ 7,5 CU UNPERF 2000MM - 0801762



NS 35/ 7,5 CAP - 1206560



Terminal marking

ZB 10:UNBEDRUCKT - 1053001



Installation level terminal block - STN 16 - 3038286

accessories

UC-TM 10 - 0818069



UCT-TM 10 - 0829142



Labeled terminal marker

ZB 10 CUS - 0824941



UC-TM 10 CUS - 0824605



UCT-TM 10 CUS - 0829623



Drawings

Installation level terminal block - STN 16 - 3038286

Circuit diagram



© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>