

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 4

Revision: 21.07.2014

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

**Trade name:** SONAX Chrome- & Alupaste

**Article number:** 308000

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

##### Sector of Use

SU21 Consumer uses: Private households / general public / consumers

SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)

**Product category** PC31 Polishes and wax blends

**Application of the substance / the mixture** Car care product

#### 1.3 Details of the supplier of the safety data sheet

##### Manufacturer/Supplier:

SONAX GmbH

Münchener Straße 75

D-86633 Neuburg (Donau)

Tel.: ++49 (0)8431/53-0

##### Further information obtainable from:

Product safety

E-mail: erp@sonax.de

Phone: + +49 (0) 8431 53 217

**1.4 Emergency telephone number:** Emergency Phone Munich Tel.: +49 (0)89 19240

### SECTION 2: Hazards identification

#### 2.1 Classification of the substance or mixture

**Classification according to Regulation (EC) No 1272/2008**

The product is not classified according to the CLP regulation.

**Classification according to Directive 67/548/EEC or Directive 1999/45/EC** Not applicable.

#### 2.2 Label elements

**Labelling according to Regulation (EC) No 1272/2008** Void

**Hazard pictograms** Void

**Signal word** Void

**Hazard statements** Void

**Precautionary statements** P102 Keep out of reach of children.

#### 2.3 Other hazards

##### Results of PBT and vPvB assessment

**PBT:** Not applicable.

**vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

**Description:** Emulsion with abrasives and additives

**Dangerous components:** Void

**Regulation (EC) No 648/2004 on detergents / Labelling for contents**

methylisothiazolinone, benzisothiazolinone, sodium pyrithione

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

##### General information:

No special measures required.

Remove soiled clothing

**After inhalation:** No special measures required

##### After skin contact:

Generally the product does not irritate the skin.

Wash the areas of skin affected with water and a mild detergent.

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 4

Revision: 21.07.2014

**Trade name: SONAX Chrome- & Alupaste**

(Contd. of page 1)

**After eye contact:***Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.***After swallowing:***Rinse out mouth and then drink plenty of water.**Do not induce vomiting; call for medical help immediately.***4.2 Most important symptoms and effects, both acute and delayed***No further relevant information available.***4.3 Indication of any immediate medical attention and special treatment needed***Treatment in accordance with the doctor's assessment of the patient's condition. Symptomatic treatment.***SECTION 5: Firefighting measures****5.1 Extinguishing media***Suitable extinguishing agents: Use fire extinguishing methods suitable to surrounding conditions.***5.2 Special hazards arising from the substance or mixture** *No further relevant information available.***5.3 Advice for firefighters***Protective equipment: The normal measures for firefighting are to be taken.***SECTION 6: Accidental release measures****6.1 Personal precautions, protective equipment and emergency procedures** *Ensure adequate ventilation***6.2 Environmental precautions:***Do not allow to penetrate the ground/soil.**Do not allow to enter sewers/ surface or ground water.***6.3 Methods and material for containment and cleaning up:***Pick up mechanically.**Flush away residues with water.**Dispose of the material collected according to regulations.***6.4 Reference to other sections***See Section 7 for information on safe handling.**See Section 8 for information on personal protection equipment.**See Section 13 for disposal information.***SECTION 7: Handling and storage****7.1 Precautions for safe handling** *No special precautions are necessary if used correctly.***Information about fire - and explosion protection:** *No special measures required.***7.2 Conditions for safe storage, including any incompatibilities****Storage:****Requirements to be met by storerooms and receptacles:** *Provide solvent resistant, sealed floor.***Information about storage in one common storage facility:** *Store away from foodstuffs.***Further information about storage conditions:***Protect from frost.**Recommended storage temperature: 20 °C.***7.3 Specific end use(s)** *No further relevant information available.***SECTION 8: Exposure controls/personal protection****8.1 Control parameters****Ingredients with limit values that require monitoring at the workplace:***The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.***Additional information:** *The lists valid during the making were used as basis.***8.2 Exposure controls****Personal protective equipment:****General protective and hygienic measures:***The usual precautionary measures are to be adhered to when handling chemicals.*

(Contd. on page 3)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 4

Revision: 21.07.2014

Trade name: SONAX Chrome- &amp; Alupaste

(Contd. of page 2)

Wash hands before breaks and at the end of work.

Keep away from foodstuffs, beverages and feed.

**Respiratory protection:**

Not required in normal cases

Ensure good ventilation/exhaustion at the workplace.

**Protection of hands:** Not required in normal cases**Eye protection:** Not required in normal cases**SECTION 9: Physical and chemical properties****9.1 Information on basic physical and chemical properties****General Information****Appearance:**

<b>Form:</b>	Pasty
<b>Colour:</b>	Beige
<b>Odour:</b>	Characteristic
<b>Odour threshold:</b>	Not determined.

<b>pH-value at 20 °C:</b>	7.5 - 8.0
---------------------------	-----------

**Change in condition**

<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	100 - 190 °C

<b>Flash point:</b>	Not applicable.
---------------------	-----------------

<b>Flammability (solid, gaseous):</b>	Not applicable.
---------------------------------------	-----------------

**Ignition temperature:**

<b>Decomposition temperature:</b>	Not determined.
-----------------------------------	-----------------

<b>Self-igniting:</b>	Product is not selfigniting.
-----------------------	------------------------------

<b>Danger of explosion:</b>	Product does not present an explosion hazard.
-----------------------------	---

**Explosion limits:**

<b>Lower:</b>	Not determined.
<b>Upper:</b>	Not determined.

<b>Vapour pressure:</b>	Not determined.
-------------------------	-----------------

<b>Density at 20 °C:</b>	1.20 - 1.23 g/cm <sup>3</sup>
--------------------------	-------------------------------

<b>Relative density</b>	Not determined.
-------------------------	-----------------

<b>Vapour density</b>	Not determined.
-----------------------	-----------------

<b>Evaporation rate</b>	Not determined.
-------------------------	-----------------

**Solubility in / Miscibility with**

<b>water:</b>	Partly miscible.
---------------	------------------

<b>Partition coefficient (n-octanol/water):</b>	Not determined.
---	-----------------

**Viscosity:**

<b>Flow time at 20 °C</b>	>60 s (DIN EN ISO 2431/6mm)
<b>Dynamic at 20 °C:</b>	20 000 - 30 000 mPas
<b>Kinematic at 40 °C:</b>	>20.5 mm <sup>2</sup> /s

<b>9.2 Other information</b>	No further relevant information available.
------------------------------	--

**SECTION 10: Stability and reactivity**

<b>10.1 Reactivity</b>	No dangerous reactions known.
------------------------	-------------------------------

<b>10.2 Chemical stability</b>	Stable under normal conditions.
--------------------------------	---------------------------------

<b>10.3 Possibility of hazardous reactions</b>	No dangerous reactions known.
--	-------------------------------

<b>10.4 Conditions to avoid</b>	See Section 7 for information on safe handling.
---------------------------------	---

**10.5 Incompatible materials:**

strong oxidizing agents

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 4

Revision: 21.07.2014

Trade name: SONAX Chrome- &amp; Alupaste

acids

(Contd. of page 3)

10.6 Hazardous decomposition products: No dangerous decomposition products known.

**SECTION 11: Toxicological information**

11.1 Information on toxicological effects There are no toxicological findings on this mixture.

**Acute toxicity****Primary irritant effect:****Skin corrosion/irritation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

**Serious eye damage/irritation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

**Respiratory or skin sensitisation**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

**Additional toxicological information:**

The product is not subject to classification according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version.

When used and handled according to specifications, the product does not have any harmful effects to our experience and the information provided to us.

**Repeated dose toxicity**

On the basis of the available data, the classification criteria are not complied with (Conventional Method).

**CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**

None of the ingredients are known to have effects which are carcinogenic, mutagenic or harmful to reproduction.

**SECTION 12: Ecological information**

12.1 Toxicity There are no ecotoxicological data available on this mixture.

**Aquatic toxicity:** No further relevant information available.

12.2 Persistence and degradability No further relevant information available.

12.3 Bioaccumulative potential No further relevant information available.

12.4 Mobility in soil No further relevant information available.

**Additional ecological information:****General notes:** The product may not be released into the environment without control.**12.5 Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.

12.6 Other adverse effects No further relevant information available.

**SECTION 13: Disposal considerations****13.1 Waste treatment methods****Recommendation**

Waste must be disposed of while observing the local, official regulations.

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

**European waste catalogue**

1) Disposal / product

2) Disposal / contaminated packaging

20 01 13\* solvents

15 01 02 plastic packaging

**SECTION 14: Transport information****14.1 UN-Number**

ADR, IMDG, IATA

Void

(Contd. on page 5)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 12.09.2015

Version: 4

Revision: 21.07.2014

Trade name: SONAX Chrome- &amp; Alupaste

(Contd. of page 4)

**14.2 UN proper shipping name**  
ADR, IMDG, IATA                      Void

**14.3 Transport hazard class(es)**  
ADR, ADN, IMDG, IATA  
Class                                      Void

**14.4 Packing group**  
ADR, IMDG, IATA                      Void

**14.5 Environmental hazards:**  
Marine pollutant:                      No

**14.6 Special precautions for user** Not applicable.

**UN "Model Regulation":**                      -

### SECTION 15: Regulatory information

#### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

##### National regulations:

##### Information about limitation of use:

Employment restrictions concerning juveniles must be observed.

Employment restrictions concerning pregnant and lactating women must be observed.

**15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### Abbreviations and acronyms:

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

NOEL = No Observed Effect Level

NOEC = No Observed Effect Concentration

LC = letal Concentration

EC50 = half maximal effective concentraion

log POW = Octanol / water partition coefficient

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

IOELV = indicative occupational exposure limit values

**\* Data compared to the previous version altered.**